



Ortronics
TRACJACK FACEPLATE, ONE-PORT (SINGLE GANG), PLASTIC
Part No. 40300549-13



Accepts front-loading TracJack modules and includes two snap-in label fields. Available in 1, 2, 3, 4 gangs. In addition to the Plastic TracJack Faceplate, Legrand offers a full range of TracJack faceplates in stainless steel, with a variety of port capacities to match your workstation applications. All TracJack plates offer recessed label fields.

Features & Benefits

Low profile design: Blends with most environments.

Recessed label fields: Supports TIA/EIA 606 standard.

Easily accepts snap-in TracJacks: Easily field configured.

Front-load module approach: Improves access for future work.

Textured finish: Hides future scuffs.

Oval mounting holes: Assists proper alignment

Compatible with all Tracjack adapters and connectors, including shielded

Specifications

General Info

Product Line	Ortronics	Color	Electrical Ivory
Finish	Smooth	UPC Number	662875294238
Country Of Origin	Taiwan, Province Of China	Material	Plastic
Features	Front Loading, Label Field	Included	Label Field, Mounting Hardware
Wall Plate Type	Networking	Application Sector	Commercial
Standard	UL Standard	Warranty Type	5-Year
Type	Workstation		

Dimensions

Product Width US	2.74 in	Product Depth US	0.31 in
Product Height US	4.5 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Compatibility	TracJack
Number of Ports	1	Operating Temperature Max	60 °C
Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Operating Temperature	-10°-60°C
Orientation	Vertical		