



Ortronics
Clarity 6 12-port Category 6 mini patch panel - hinged mounting - 10 in x 2.5 in
Part No. PMP612H



Clarity 6 12-Port Category 6 mini patch panel is component compliant to EIA/TIA Category 6 performance requirements. The panel measures 10" x 2.5". Jacks are grouped in six-port modules. Part of the Clarity 6 link and channel solution that provides significant installed performance headroom.

Features & Benefits

- ETL verified to TIA Category 6 component spec: Ensures component performance.
- Center tuned to Clarity 6 patch cords: More transparent mated union.
- Universally wired 110 termination: Supports T568A and T568B installs.
- New IDC housing: Handles larger Category 6 conductors.
- Supplied rear cable management: Supports good cabling practice.
- High density design: Maximizes rack utilization.
- RoHS compliant: Lead free.

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875462439	Country Of Origin	United States
Material	Steel	Application Sector	Commercial, Industrial
Standard	RoHS	Warranty Type	5-Year
Type	Panel		

Dimensions

Product Width US	10.0 in	Product Depth US	3.43 in
Product Height US	2.5 in		

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----

Technical Information

Category Performance Application	Cat6	Wire Gauge	22-24 AWG
Number of Ports	12	Shielded/Unshielded Cable	Unshielded
Wattage	100 W	Voltage	60.0 V
