



TracJack Stylistics Plastic Duplex Frame accepts three front-loading TracJack modules in the rectangular electrical mounting footprint of a GFCI outlet. It is compatible with many cable delivery systems that can house electrical duplex outlets

Features & Benefits

Matches rectangular electrical outlet (GFI) footprint: Supports use with electrical delivery system.

Field configurable with TracJacks: Design or site flexibility for new or retrofit.

Supports TracJack footprint: Broad offering of connector options.

Front load and access: Connector access without removing plate.

Choice of colors: Compatible with many environments.

Specifications

General Info

Product Line	Ortronics	Color	Cloud White
Finish	Smooth	UPC Number	662875344261
Country Of Origin	Taiwan, Province Of China	Material	Plastic
Wall Plate Type	Networking	Application Sector	Commercial
Standard	UL Standard	Warranty Type	5-Year
Type	Workstation		

Dimensions

Product Width US	1.75 in	Product Depth US	0.45 in
------------------	---------	------------------	---------

Product Height US	4.24 in
-------------------	---------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Compatibility	TracJack
---------------------------	--------	---------------	----------

Number of Ports	2	Operating Temperature Max	60 °C
-----------------	---	---------------------------	-------

Number of Gangs	1	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Exposed Screws	Operating Temperature	-10°-60°C
---------------	----------------	-----------------------	-----------

Orientation	Vertical
-------------	----------