



TracJack Stylistics Plastic Duplex Frame accepts four front-loading TracJack modules in the rectangular electrical mounting footprint of a GFCI outlet. It is compatible with many cable delivery systems that can house electrical duplex outlets

## Features & Benefits

Matches rectangular electrical outlet (GFI) footprint: Supports use with electrical delivery system.

Field configurable with TracJacks: Design or site flexibility for new or retrofit.

Supports TracJack footprint: Broad offering of connector options.

## Specifications

### General Info

Product Line	Ortronics	Color	Cloud White
Finish	Smooth	UPC Number	662875370635
Country Of Origin	Taiwan, Province Of China	Material	Plastic
Wall Plate Type	Networking	Application Sector	Commercial
Standard	UL Standard	Warranty Type	5-Year
Type	Workstation		

### Dimensions

Product Width US	1.75 in	Product Depth US	0.45 in
Product Height US	4.27 in		

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

Operating Temperature Min	-10 °C	Compatibility	TracJack
Number of Ports	4	Operating Temperature Max	60 °C
Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Exposed Screws	Operating Temperature	-10°-60°C
Orientation	Vertical		

---