



This plate accepts three TracJack modules or blanks. Use with 40700071, 40700072, or 40700073 bezels, to snap mount into 2.70" x 1.375" TIA referenced furniture openings for Steelcase, Haworth, Knoll and others. 5 pack.

Features & Benefits

- Field configurable with TracJacks: Supports use with electrical delivery system
- Supports TracJack footprint: Design or site flexibility for new or retrofit.
- Front load and access: Broad offering of connector options.
- Choice of colors: Compatible with many environments.

Specifications

General Info

Product Line	Ortronics	Color	Black
Finish	Smooth	UPC Number	662875491828
Country Of Origin	Taiwan, Province Of China	Material	Plastic
Features	Rear Loading	Wall Plate Type	Networking
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Insert

Dimensions

Product Width US	2.66 in	Product Depth US	0.68 in
Product Height US	1.33 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Compatibility	TracJack
Number of Ports	3	Operating Temperature Max	60 °C
Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Screwless	Operating Temperature	-10°-60°C
Orientation	Vertical		

