



Clarity 5E Modular Patch Cord, 7', white

Features & Benefits

Center tuned to Clarity jacks and panels for a more transparent mated union
 Narrow Paralign plug profile supports use in high density panels and hubs

Paralign™ 2 plug termination better controls plug performance

Icon compatible – provides additional TIA-606-A designation capabilities

Assembled with premium cordage, 100% factory tested for performance, reliability and long life

Specifications

General Info

| | | | |
|--------------|---------------------------------------|--------------------|------------------------|
| Product Line | Ortronics | Color | White |
| UPC Number | 662875450054 | Country Of Origin | Mexico |
| Features | Standard Diameter | Application Sector | Commercial, Industrial |
| Standard | ANSI/TIA-568.E-2;ISO/IEC 11801-1;RoHS | Warranty Type | 5-Year |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|--------|--------------|------|
| Product Length US | 7.0 FT | Cable Length | 7 ft |
|-------------------|--------|--------------|------|

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|---------------------------|--------|----------------------------------|-------|
| Operating Temperature Min | -10 °C | Category Performance Application | Cat5e |
|---------------------------|--------|----------------------------------|-------|

| | | | |
|---------------|-------|------------|--------|
| Compatibility | RJ-45 | Wire Gauge | 24 AWG |
|---------------|-------|------------|--------|

| | | | |
|------------------|---------------------------|-----------------------|--------------|
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 μ in Gold |
|------------------|---------------------------|-----------------------|--------------|

| | | | |
|--------------------|-------------|-------------|---------|
| Jacket Application | Riser Rated | Bend Radius | 0.86 in |
|--------------------|-------------|-------------|---------|

| | | | |
|---------------------------|------------|-------------------|----------------|
| Shielded/Unshielded Cable | Unshielded | Termination Style | Pre-Terminated |
|---------------------------|------------|-------------------|----------------|

| | | | |
|---------------------|----------|---------------------------|-------|
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
|---------------------|----------|---------------------------|-------|

| | | | |
|------------|------------|---------------|----------|
| Cable Type | Non-Booted | Jacket Rating | CM Rated |
|------------|------------|---------------|----------|

| | | | |
|----------------|----------|-------|--------------------|
| Cable Diameter | 0.215 in | Braid | Non-braided Wiring |
|----------------|----------|-------|--------------------|

| | | | |
|-------------|------------|-------------|------------|
| Connector 2 | RJ-45 Male | Connector 1 | RJ-45 Male |
|-------------|------------|-------------|------------|

| | | | |
|-----------------------|-----------|--------------------|---------------------------|
| Operating Temperature | -10°-60°C | Operating Humidity | 0-90% RH (Non-Condensing) |
|-----------------------|-----------|--------------------|---------------------------|

| | | | |
|-------------------|---|--------------------|--------|
| Number of Strands | 7 | Conductor Material | Copper |
|-------------------|---|--------------------|--------|

| | | | |
|---------|---------|------------------------|---------|
| Voltage | 300.0 V | Connectivity Footprint | Clarity |
|---------|---------|------------------------|---------|

| | |
|---------------------|--------------|
| Storage Temperature | -40° - 60° C |
|---------------------|--------------|
