



Accepts front-loading TracJack modules and includes two snap-in label fields. Available in 1, 2, 3, 4 gangs. In addition to the Plastic TracJack Faceplate, Legrand offers a full range of TracJack faceplates in stainless steel, with a variety of port capacities to match your workstation applications. All TracJack plates offer recessed label fields.

## Features & Benefits

Low profile design: Blends with most environments.

Recessed label fields: Supports TIA/EIA 606 standard.

Easily accepts snap-in TracJacks: Easily field configured.

Front-load module approach: Improves access for future work.

Textured finish: Hides future scuffs.

Oval mounting holes: Assists proper alignment

Compatible with all Tracjack adapters and connectors, including shielded

## Specifications

### General Info

|                   |                            |                    |                                |
|-------------------|----------------------------|--------------------|--------------------------------|
| Product Line      | Ortronics                  | Color              | Electrical Ivory               |
| Finish            | Smooth                     | UPC Number         | 662875294252                   |
| Country Of Origin | Taiwan, Province Of China  | Material           | Plastic                        |
| Features          | Front Loading, Label Field | Included           | Label Field, Mounting Hardware |
| Wall Plate Type   | Networking                 | Application Sector | Commercial                     |
| Standard          | UL Standard                | Warranty Type      | 5-Year                         |
| Type              | Workstation                |                    |                                |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 2.74 in | Product Depth US | 0.31 in |
| Product Height US | 4.5 in  |                  |         |

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                           |             |                           |           |
|---------------------------|-------------|---------------------------|-----------|
| Operating Temperature Min | -10 °C      | Compatibility             | TracJack  |
| Number of Ports           | 3           | Operating Temperature Max | 60 °C     |
| Number of Gangs           | 1           | Indoor/Outdoor            | Indoor    |
| Mounting Type             | Box Mounted | Operating Temperature     | -10°-60°C |
| Orientation               | Vertical    |                           |           |