



Ortronics  
**TRACJACK FACEPLATE, EIGHT-PORT (DUAL GANG), PLASTIC**  
Part No. 40300554-88



Accepts front-loading TracJack modules and includes two snap-in label fields. Available in 1, 2, 3, 4 gangs. In addition to the Plastic TracJack Faceplate, Legrand offers a full range of TracJack faceplates in stainless steel, with a variety of port capacities to match your workstation applications. All TracJack plates offer recessed label fields.

## Features & Benefits

- Low profile design: Blends with most environments.
- Easily accepts snap-in TracJacks: Easily field configured.
- Textured finish: Hides future scuffs.
- Recessed label fields: Supports TIA/EIA 606 standard.
- Front-load module approach: Improves access for future work.

## Specifications

### General Info

Product Line	Ortronics	Color	Cloud White
Finish	Smooth	UPC Number	662875326663
Country Of Origin	Malaysia	Material	Plastic
Features	Front Loading, Label Field	Included	Label Field, Mounting Hardware
Wall Plate Type	Networking	Application Sector	Commercial
Standard	UL Standard	Warranty Type	5-Year
Type	Workstation		

### Dimensions

Product Width US	2.74 in	Product Depth US	0.31 in
------------------	---------	------------------	---------

Product Height US	4.5 in
-------------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-10 °C	Compatibility	TracJack
---------------------------	--------	---------------	----------

Number of Ports	8	Operating Temperature Max	60 °C
-----------------	---	---------------------------	-------

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

Mounting Type	Box Mounted	Operating Temperature	-10°-60°C
---------------	-------------	-----------------------	-----------

Orientation	Vertical
-------------	----------