



Accepts front-loading TracJack modules and includes two snap-in label fields. Available in 1, 2, 3, 4 gangs. In addition to the Plastic TracJack Faceplate, Legrand offers a full range of TracJack faceplates in stainless steel, with a variety of port capacities to match your workstation applications. All TracJack plates offer recessed label fields.

## Features & Benefits

Low profile design: Blends with most environments.	Recessed label fields: Supports TIA/EIA 606 standard.
Easily accepts snap-in TracJacks: Easily field configured.	Front-load module approach: Improves access for future work.
Textured finish: Hides future scuffs.	Compatible with all Tracjack adapters and connectors, including shielded

## Specifications

### General Info

Product Line	Ortronics	Color	Cloud White
Finish	Smooth	UPC Number	662875394709
Country Of Origin	Taiwan, Province Of China	Material	Plastic
Features	Front Loading, Label Field	Wall Plate Type	Networking
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Workstation

### Dimensions

Product Width US	4.05 in	Product Depth US	0.31 in
Product Height US	2.11 in		

---

Additional Information

---

Product Environmental Profile    Yes

---

Technical Information

---

Operating Temperature Min	-10 °C	Compatibility	TracJack
Number of Ports	12	Operating Temperature Max	60 °C
Number of Gangs	2	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Operating Temperature	-10°-60°C
Orientation	Vertical		

---