



Quiktron
Q-Series Patch Cords, CAT6, booted, White, 5 FT
Part No. 576-125-005



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

Product Line	Quiktron	Color	White
UPC Number	884815779999	Country Of Origin	Vietnam
Features	Standard Diameter	Application Sector	Commercial, Industrial
Warranty Type	5-Year	Type	Copper Patch Cord

Dimensions

Product Weight US	0.125 lb	Product Length US	5.0 FT
Cable Length	5 ft		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-10 °C	Category Performance Application	Cat6
Compatibility	RJ-45	Wire Gauge	26 AWG
Storage Humidity	0-90% RH (Non-Condensing)	Plating Specification	50 μ in Gold
Jacket Application	Riser Rated	Bend Radius	0.896 in
Shielded/Unshielded Cable	Unshielded	Termination Style	Pre-Terminated
Conductor Stranding	Stranded	Operating Temperature Max	60 °C
Cable Type	Snagless	Jacket Rating	CM Rated
Cable Diameter	0.224 in	Braid	Non-braided Wiring
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Operating Temperature	-10°-60°C	Operating Humidity	0-90% RH (Non-Condensing)
Number of Strands	7	Conductor Material	Copper
Voltage	300.0 V	Storage Temperature	-40° - 60° C
