



Quiktron  
Q-Series Patch Cords, CAT6, booted, White, 10 FT  
Part No. 576-125-010



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

|               |                   |                    |                        |
|---------------|-------------------|--------------------|------------------------|
| Product Line  | Quiktron          | Color              | White                  |
| UPC Number    | 884815780018      | Country Of Origin  | Vietnam                |
| Features      | Standard Diameter | Application Sector | Commercial, Industrial |
| Warranty Type | 5-Year            | Type               | Copper Patch Cord      |

### Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Weight US | 0.25 lb | Product Length US | 10.0 FT |
| Cable Length      | 10 ft   |                   |         |

### Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|                           |                           |                                  |                           |
|---------------------------|---------------------------|----------------------------------|---------------------------|
| Operating Temperature Min | -10 °C                    | Category Performance Application | Cat6                      |
| Compatibility             | RJ-45                     | Wire Gauge                       | 26 AWG                    |
| Storage Humidity          | 0-90% RH (Non-Condensing) | Plating Specification            | 50 μ in Gold              |
| Jacket Application        | Riser Rated               | Bend Radius                      | 0.896 in                  |
| Shielded/Unshielded Cable | Unshielded                | Termination Style                | Pre-Terminated            |
| Conductor Stranding       | Stranded                  | Operating Temperature Max        | 60 °C                     |
| Cable Type                | Snagless                  | Jacket Rating                    | CM Rated                  |
| Cable Diameter            | 0.224 in                  | Braid                            | Non-braided Wiring        |
| Connector 2               | RJ-45 Male                | Connector 1                      | RJ-45 Male                |
| Operating Temperature     | -10°-60°C                 | Operating Humidity               | 0-90% RH (Non-Condensing) |
| Number of Strands         | 7                         | Conductor Material               | Copper                    |
| Voltage                   | 300.0 V                   | Storage Temperature              | -40° - 60° C              |

---