

TR26342DVSGRY
Tool-less Decorator 20A/125V


Tool-free terminations brought to you by Legrand

TR26342DVSW

The PowerHold™ receptacle device maximizes contractor productivity, reduces errors, and enhances profitability while delivering faster, more reliable results. With fast terminations, superior wiring retention and color-coded levers that ensure accurate connections, this standard receptacle makes the installation process quick, easy, and safe. Best suited for MDU, hospitality, prefab, and commercial applications.

Features & Benefits

- **Patented Terminal Design:** Toothed design to provide a secure connection for solid and stranded copper wire from #14 AWG to #10 AWG.
- **Superior Wire Retention:** Retention force greater than 30 lbs. ensures consistent, reliable connections*.
- **Error-Free Installation:** Color-coded levers to reduce the risk of miswiring, while an audible snap confirms a securely closed lever.
- **Safe Easy Wiring:** No exposed live terminals.
- **Impact- Resistant:** Nylon face for durability.
- **Triple Wipe Brass Power Contacts:** For lasting retention.
- **Fast Terminations:** Wire our device in under 10 seconds, boost productivity and finish ahead of schedule.
- **Dual Split Circuit:** Only tool-less device on the market to allow breaking the hot and neutral tabs to help prevent overloading a circuit with a shared neutral.
- **Sleek, Space- Saving Design:** Shallowest design on the market without compromising on performance.
- **Robust and Ergonomic Levers:** Make terminations easier with larger levers.
- **Easy to Clean:** Chemical-resistant face.



TR26342DVS

Vertical Markets

- | | | | |
|---------------|------------------|------------------|---------------|
| ▪ Commercial | ▪ Retail | ▪ Multi Dwelling | ▪ Hospitality |
| ▪ Residential | ▪ Prefabrication | ▪ Education | |

Compliance



UL Listed, File Number E140596,

Standard UL498, CSA/CUL approved, Standard CSA 22.2 No. 42 General Use Receptacles, Conforms to NEMA® WD-1 and WD-6

*based on #12 AWG Solid Copper

Technical Information

Performance

Electrical

Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

Terminal Identification	Terminal levers identified in accordance with UL498 (Black, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are permanent part of device

Material Specs


Face	Nylon - Impact-Resistant
Body	Nylon - Impact-Resistant
Line Contacts	.031 Copper Alloy
Mounting Strap	.040 Zinc-Plated Steel
Ground Contacts	.012 Brass Alloy
Tamper-Resistant Shutters	Thermoplastic
Flat Head Mounting Screws	Zinc-Plated Steel
Auto-Ground Clip	Stainless Steel - Nickel-Plated
Mounting Screws	Tri-Drive Steel

Environmental

Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)
Flammability	UL94 V2
Only for indoor use	Nickel Plated Brass

Warranty

1 year



Depth (into Wallbox) = 1.05"
TR26342DVSLA



Ordering Information

Catalog Number	Description	Ratings	Color	NEMA Config.
TR15DVS	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Brown	5-15R
TR15DVSBK	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Black	5-15R
TR15DVSBLL	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Blue	5-15R
TR15DVSGRY	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Gray	5-15R
TR15DVSI	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Ivory	5-15R
TR15DVSLA	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Light Almond	5-15R
TR15DVSOR	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Orange	5-15R
TR15DVSRED	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	Red	5-15R
TR15DVSW	PowerHold™ TR15 Tool-less Duplex Receptacle	15A , 125V	White	5-15R
TR20DVS	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Brown	5-20R
TR20DVSBK	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Black	5-20R
TR20DVSBLL	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Blue	5-20R
TR20DVSGRY	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Gray	5-20R
TR20DVSI	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Ivory	5-20R
TR20DVSLA	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Light Almond	5-20R
TR20DVSOR	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Orange	5-20R
TR20DVSRED	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	Red	5-20R
TR20DVSW	PowerHold™ TR20 Tool-less Duplex Receptacle	20A , 125V	White	5-20R
TR26242DVS	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Brown	5-20R
TR26242DVSBK	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Black	5-15R
TR26242DVSBLL	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Blue	5-15R
TR26242DVSGRY	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Gray	5-15R
TR26242DVSI	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Ivory	5-15R
TR26242DVSLA	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Light Almond	5-15R
TR26242DVSOR	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Orange	5-15R
TR26242DVSRED	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	Red	5-15R
TR26242DVSW	PowerHold™ TR26242 Tool-less Decorator Receptacle	15A , 125V	White	5-15R
TR26342DVS	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Brown	5-20R
TR26342DVSBK	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Black	5-20R
TR26342DVSBLL	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Blue	5-20R
TR26342DVSGRY	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Gray	5-20R
TR26342DVSI	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Ivory	5-20R
TR26342DVSLA	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Light Almond	5-20R
TR26342DVSOR	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Orange	5-20R
TR26342DVSRED	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	Red	5-20R
TR26342DVSW	PowerHold™ TR26342 Tool-less Decorator Receptacle	20A/125V	White	5-20R


NEMA
5-15R

NEMA
5-20R

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1-877-295-3472
www.legrand.us

Canada
1-844-977-3783
www.legrand.ca

FOLLOW US

