



One piece, heavy steel wall plates offered in 10 and 14 gauge. Ideal solution for behavioral health facilities as well as correctional facilities. The ligature-resistant construction coupled with painted cold rolled steel or brushed stainless options provides a unique blend of features when security and safety are key priorities. Traditional mounting is also available with backplate as well as pour-in-place concrete solutions.

### Features & Benefits

Robust design available in 10 & 14 gauge painted cold roll steel (White or Ivory) as well as 14 gauge painted Stainless Steel and Brushed Stainless Steel	Versatile product available in 1-3 gangs and a wide range of device openings including blank, duplex, decorator, round opening and a toggle
Wall plate mounting with two solutions for installation with an 11 gauge galvanized steel plate. Pick between a surface-mounted solution or a pour-in-place on a junction box	Back plate-mounted ground wire lead to ensure a proper code compliant solution to UL
Industry-leading combinations to meet customers' everyday needs	Complies with NY Behavioral Health standards
For recessed mount or pour-in-place junction boxes	Ligature-resistant construction

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	White
Finish	Painted	Material	Cold Rolled Steel
Wall Plate Type	Round	Application Sector	Commercial
Warranty Type	1-Year		

#### Dimensions

Product Width US	0.5 in	Product Weight US	2.416 lb
Product Depth US	0.5 in	Product Height US	5.5 in

Product Length US	7.34 in	Circular Outlet Diameter	1.5938 in
-------------------	---------	--------------------------	-----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	2
-----------------	---