

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0100MQMJ

Rating: 100VA
 Phase: 1
 Freq: 50/60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.1	79.4
Width	3.0	76.2
Depth	3.9	98.1

	lbs	kg
Weight	2.6	1.2

PRIMARY		SECONDARY	
Voltage	240x480	Voltage	120x240
Connection	Parallel x Series (Vx2V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 205 VA
	10% Voltage Drop @ 275 VA
	15% Voltage Drop @ 340 VA
Full Load Watts Loss	20.4 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394