

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E0150KHP

Rating: 150VA
 Phase: 1
 Freq: 50/60 Hz
 Temp. Rise: 80°C
 Enclosure: NEMA Type 1
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.7	94.1
Width	3.1	78.6
Depth	6.6	167.9

	lbs	kg
Weight	3.8	1.7

PRIMARY		SECONDARY	
Voltage	347/380	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 320 VA
	10% Voltage Drop @ 445 VA
	15% Voltage Drop @ 560 VA
Full Load Watts Loss	24.8 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394