

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E0250KHP

Rating: 250VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: NEMA Type 1
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	4.2	107
Width	3.9	98.6
Depth	6.6	168

	lbs	kg
Weight	5.7	2.6

PRIMARY		SECONDARY	
Voltage	347/380	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 520 VA
	10% Voltage Drop @ 800 VA
	15% Voltage Drop @ 1060 VA
Full Load Watts Loss	27.4 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394