

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E0500KHP

Rating: 500VA
 Phase: 1
 Freq: 50/60 Hz
 Temp. Rise: 80°C
 Enclosure: NEMA Type 1
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	4.7	119.3
Width	4.6	116.7
Depth	7.2	183.4

	lbs	kg
Weight	10.6	4.8

PRIMARY		SECONDARY	
Voltage	347/380	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 1275 VA
	10% Voltage Drop @ 2080 VA
	15% Voltage Drop @ 2820 VA
Full Load Watts Loss	42.3 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394