

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E1000KHP

Rating: 1.0KVA
 Phase: 1
 Freq: 50/60 Hz
 Temp. Rise: 80°C
 Enclosure: NEMA Type 1
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	5.2	132.3
Width	5.3	135.7
Depth	8.4	213.4

	lbs	kg
Weight	20.7	9.4

PRIMARY		SECONDARY	
Voltage	347/380	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 3385 VA
	10% Voltage Drop @ 5405 VA
	15% Voltage Drop @ 7280 VA
Full Load Watts Loss	69.8 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394