

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E0050PR

Rating: 50VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: NEMA Type 1
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.4	87.2
Width	2.7	68.5
Depth	6.1	154

	lbs	kg
Weight	1.7	0.8

PRIMARY		SECONDARY	
Voltage	120X240	Voltage	24
Connection	Parallel x Series (Vx2V)	Connection	Series (V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 90 VA
	10% Voltage Drop @ 115 VA
	15% Voltage Drop @ 140 VA
Full Load Watts Loss	13.5 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394