

PRODUCT DATA SHEET

General Purpose Enclosed Control Transformer

Cat. Number: C2E0150PR

Rating: 150VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: NEMA Type 1
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.7	94.1
Width	3.1	78.6
Depth	6.6	167.9

	lbs	kg
Weight	3.8	1.7

PRIMARY		SECONDARY	
Voltage	120X240	Voltage	24
Connection	Parallel x Series (Vx2V)	Connection	Series (V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 300 VA
	10% Voltage Drop @ 435 VA
	15% Voltage Drop @ 560 VA
Full Load Watts Loss	25 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394