

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0050ACP

Rating: 50VA
Phase: 1
Freq: 60 Hz
Temp. Rise: 80°C
Enclosure: Core & Coil
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	2.9	72.7
Width	2.6	66.7
Depth	3.9	100.1

	lbs	kg
Weight	1.9	0.9

PRIMARY		SECONDARY	
Voltage	480/600	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 95 VA
	10% Voltage Drop @ 125 VA
	15% Voltage Drop @ 150 VA
Full Load Watts Loss	15.3 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394