

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0100ACP

Rating: 100VA
 Phase: 1
 Freq: 60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.1	79.4
Width	3.0	76.2
Depth	3.9	98.1

	lbs	kg
Weight	2.6	1.2

PRIMARY		SECONDARY	
Voltage	480/600	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 210 VA
	10% Voltage Drop @ 290 VA
	15% Voltage Drop @ 365 VA
Full Load Watts Loss	20.4 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394