

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0500ACP

Rating: 500VA
 Phase: 1
 Freq: 60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	4.2	107.2
Width	4.5	114.3
Depth	4.8	122.1

	lbs	kg
Weight	10.5	4.8

PRIMARY		SECONDARY	
Voltage	480/600	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 1375 VA
	10% Voltage Drop @ 2380 VA
	15% Voltage Drop @ 3310 VA
Full Load Watts Loss	43.8 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394