

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G2000ACP

Rating: 2.0KVA
 Phase: 1
 Freq: 60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 180°C

DIMENSIONS		
	in	mm
Height	5.7	144.8
Width	6.4	161.9
Depth	7.2	184.1

	lbs	kg
Weight	35.4	16.0

PRIMARY		SECONDARY	
Voltage	480/600	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 7050 VA
	10% Voltage Drop @ 12315 VA
	15% Voltage Drop @ 17285 VA
Full Load Watts Loss	121.8 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394