

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G3000ACP

Rating: 3.0KVA
 Phase: 1
 Freq: 60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 180°C

DIMENSIONS		
	in	mm
Height	6.7	169.4
Width	7.5	190.5
Depth	8.5	215.1

	lbs	kg
Weight	56.5	25.6

PRIMARY		SECONDARY	
Voltage	480/600	Voltage	120X240
Connection	Series (V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 15945 VA
	10% Voltage Drop @ 27860 VA
	15% Voltage Drop @ 39065 VA
Full Load Watts Loss	165.3 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394