

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0250MQMJ

Rating: 250VA
 Phase: 1
 Freq: 50/60 Hz
 Temp. Rise: 80°C
 Enclosure: Core & Coil
 Material: Copper
 Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.7	94.1
Width	3.8	95.3
Depth	4.2	107.1

	lbs	kg
Weight	5.7	2.6

PRIMARY		SECONDARY	
Voltage	240x480	Voltage	120x240
Connection	Parallel x Series (Vx2V)	Connection	Parallel x Series (Vx2V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 530 VA
	10% Voltage Drop @ 840 VA
	15% Voltage Drop @ 1130 VA
Full Load Watts Loss	28.7 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394