

PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0250PR

Rating: 250VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: Core & Coil
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.7	94.1
Width	3.8	95.3
Depth	4.2	107.1

	lbs	kg
Weight	5.8	2.6

PRIMARY		SECONDARY	
Voltage	120X240	Voltage	24
Connection	Parallel x Series (Vx2V)	Connection	Series (V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 480 VA
	10% Voltage Drop @ 735 VA
	15% Voltage Drop @ 975 VA
Full Load Watts Loss	29 Watts

Country of Origin	Mexico
Certifications	CSA: LR3902, UL: E50394