

# PRODUCT DATA SHEET

Open Style Control Transformer

Cat. Number: C2G0500PR

Rating: 500VA  
Phase: 1  
Freq: 50/60 Hz  
Temp. Rise: 80°C  
Enclosure: Core & Coil  
Material: Copper  
Ins. Class: 130°C

| DIMENSIONS |     |       |
|------------|-----|-------|
|            | in  | mm    |
| Height     | 4.2 | 107.2 |
| Width      | 4.5 | 114.3 |
| Depth      | 4.8 | 122.1 |

|        | lbs  | kg  |
|--------|------|-----|
| Weight | 10.3 | 4.7 |

| PRIMARY     |                          | SECONDARY   |                |
|-------------|--------------------------|-------------|----------------|
| Voltage     | 120X240                  | Voltage     | 24             |
| Connection  | Parallel x Series (Vx2V) | Connection  | Series (V)     |
| Termination | Terminal Block           | Termination | Terminal Block |

|                                    |                         |
|------------------------------------|-------------------------|
| Load Inrush VA at 40% Power Factor | 5% Voltage Drop @ 0 VA  |
|                                    | 10% Voltage Drop @ 0 VA |
|                                    | 15% Voltage Drop @ 0 VA |
| Full Load Watts Loss               | 0 Watts                 |

|                   |                         |
|-------------------|-------------------------|
| Country of Origin | Mexico                  |
| Certifications    | CSA: LR3902, UL: E50394 |