

PRODUCT DATA SHEET

Molded Style Control Transformer

Cat. Number: C2M0050PR

Rating: 50VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: Core & Coil
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	2.9	72.7
Width	3.0	76
Depth	4.4	111.7

	lbs	kg
Weight	2.2	1.0

PRIMARY		SECONDARY	
Voltage	120X240	Voltage	24
Connection	Parallel x Series (Vx2V)	Connection	Series (V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 95 VA
	10% Voltage Drop @ 130 VA
	15% Voltage Drop @ 160 VA
Full Load Watts Loss	13.4 Watts

Country of Origin	Mexico
Certifications	UL: E50394