

PRODUCT DATA SHEET

Molded Style Control Transformer

Cat. Number: C2M0100PR

Rating: 100VA
Phase: 1
Freq: 50/60 Hz
Temp. Rise: 80°C
Enclosure: Core & Coil
Material: Copper
Ins. Class: 130°C

DIMENSIONS		
	in	mm
Height	3.1	79.4
Width	3.3	83
Depth	4.3	109.7

	lbs	kg
Weight	2.9	1.3

PRIMARY		SECONDARY	
Voltage	120X240	Voltage	24
Connection	Parallel x Series (Vx2V)	Connection	Series (V)
Termination	Terminal Block	Termination	Terminal Block

Load Inrush VA at 40% Power Factor	5% Voltage Drop @ 215 VA
	10% Voltage Drop @ 300 VA
	15% Voltage Drop @ 380 VA
Full Load Watts Loss	19 Watts

Country of Origin	Mexico
Certifications	UL: E50394