



## 32611P 13-in-1 Multi-Bit Pocket Precision Screwdriver

★★★★★ (0) [Write a review](#)

- Mini pocket screwdriver with concealable tip and a pocket clip for easy pocket storage
- Five double-ended bits include #0, #00 Phillips, #1, #2 Phillips, 3/32 and 1/8-Inch slotted tips, 3/16-Inch slotted and 3/32-Inch hex, 7/64 and 1/8-Inch hex, and 3.5 mm and 1/4-Inch nut drivers
- Multi-Bit screwdriver with rotating cap for optimum and precise control
- Versatile interchangeable barrel has a short side that functions as a magnetic pickup tool plus compact pocket storage, and a long side for bit holding.
- Rare-Earth magnet retains fasteners for one-handed driving and functions as a pickup tool
- Steel bits with heat treated precision ground tips for greater strength
- Cushion-Grip™ handle for maximum comfort when working on small equipment

The 13-in-1 Multi Bit Pocket Precision Screwdriver has a concealable tip and a pocket clip for convenient storage. Dual-length barrel allows you to flip the shaft to store in your pocket or use as a magnetic pickup tool. This driver is designed for precision work, featuring a spin cap for optimum control, outstanding comfort with our exclusive Cushion-Grip™ handle, and precision milled tips, stored in the handle, to fit screw openings securely.

### Specifications

Application:	Precision	Handle Material:	Plastic
Special Features:	Spin Cap and Cushion-Grip Handle for Great Control	Handle Color:	Yellow/Black
Nut Driver Sizes:	3.5 mm, 1/4"	Handle Length:	4.25" (10.8 cm)
Measurement Standard:	SAE, mm	Handle Diameter:	0.69" (1.8 cm)
Phillips Bits:	#00, #0, #1, #2	Color Code:	Blue
Slotted Bits:	3/32" (2.4 mm), 1/8" (3.2 mm), 3/16" (4 mm)	Overall Length:	6.51" (16.5 cm)
Hex Head Bits:	3/32", 7/64", 1/8"	Overall Height:	0.69" (1.8 cm)
Included:	(10) Bits, (2) Nut Drivers, Handle	Overall Width:	0.69" (1.8 cm)
Magnetic:	Yes	Number of Pieces:	8
Shaft Length:	2.3" (5.8 cm)	Type:	Multi-Bit Screwdriver
Material:	Steel	Weight:	0.10 lb (0.04 kg)
Insulated:	No	UPC:	092644329470
Handle Type:	Cushion-Grip™		