



32600P

## 13-in-1 All-Purpose Pocket Precision Screwdriver

★★★★★ 5.0 (1) [Write a review](#)

- Precision screwdriver with concealable tip and a pocket clip for easy storage
- Five double-ended bits in one tool, featuring #0 and #00 Phillips, #1 and #2 Phillips, 3/32, 1/8, and 3/16-Inch slotted, T15 TORX®, #1 and #2 square plus 3.5 mm and 1/4-Inch nut drivers
- Rotating cap for optimum and precise control
- Versatile interchangeable barrel has a short side that functions as a magnetic pickup tool plus compact pocket storage, and a long side for bit holding
- Rare-Earth magnet retains fasteners for one-handed driving and functions as a pickup tool
- Steel bits with heat treated precision ground tips for greater strength
- Cushion-Grip™ handle for maximum comfort when working on small equipment

The 13-in-1 All-Purpose Pocket Precision Screwdriver has a concealable tip and a pocket clip for convenient storage. Dual-length barrel allows you to flip the shaft to store in your pocket or use as a magnetic pickup tool. This driver is designed for precision work, featuring a spin cap for optimum control, outstanding comfort with our exclusive Cushion-Grip™ handle, and precision milled tips, stored in the handle, to fit screw openings securely.

### Specifications

|                       |                                    |                   |                       |
|-----------------------|------------------------------------|-------------------|-----------------------|
| Application:          | Fastening, Precision               | Handle Type:      | Cushion-Grip™         |
| Special Features:     | Spin Cap, Cushion-Grip™ Handle     | Handle Material:  | Plastic               |
| Nut Driver Sizes:     | 3.5 mm, 1/4"                       | Handle Color:     | Yellow/Black          |
| Measurement Standard: | SAE, Metric                        | Handle Length:    | 4.25" (11.4 cm)       |
| Phillips Bits:        | #00, #0, #1, #2                    | Handle Diameter:  | 0.69" (1.8 cm)        |
| Slotted Bits:         | 1/8", 3/32", 3/16"                 | Overall Length:   | 6.55" (16.6 cm)       |
| Square Bits:          | #1, #2                             | Overall Height:   | 0.68" (1.7 cm)        |
| TORX® Bits:           | T15                                | Overall Width:    | 0.78" (2 cm)          |
| Included:             | (10) Bits, (2) Nut Drivers, Handle | Number of Pieces: | 8                     |
| Magnetic:             | Yes                                | Type:             | Multi-Bit Screwdriver |
| Shaft Length:         | 2.3" (5.8 cm)                      | Weight:           | 1.6 oz (45 g)         |
| Material:             | Steel                              | UPC:              | 092644329494          |
| Insulated:            | No                                 |                   |                       |