

# RUH – OXFORD™

COMMERCIAL AND RESIDENTIAL UNIT HEATER

**OXFORD™**  
SERIES | SÉRIE



## A VERSATILE WORKHORSE

The RUH unit heater is small on price and big on heat. These heavy-duty units are well suited to situations where large amounts of heat must be provided in wide open spaces such as garages, workshops, commercial warehouses and construction sites. This unit has a powerful output up to 5000 W with a voltage of 240/208. The RUH has adjustable louvers that allow you to direct heat right from the source. With or without a built-in thermostat, it provides instant heat. Quiet, lightweight and easy-to-install with a universal wall or ceiling mounting bracket, this unit heater is everything you expect for less. Guaranteed productivity!

- **INSTANT HEAT**
- **ADJUSTABLE LOUVERS ALLOW YOU TO DIRECT HEAT**
- **WALL OR CEILING INSTALLATION SUPPORT BRACKET INCLUDED**
- **CLOSED AND PERMANENTLY LUBRICATED MOTOR**
- **2 KW TO 5 KW MODELS AVAILABLE**

### COLOUR

- charcoal

### FINISH

- epoxy-polyester powdercoat

### MANUFACTURING

- 20-gauge steel cabinet
- closed and permanently lubricated motor
- 350 CFM quiet helicoidal fan
- adjustable louvers
- thermal protection with automatic reset

### ELEMENT

- nichrome element produces instant heat

### CONTROL

- built-in thermostat (included with T series)
- wall thermostat (not included)

### INSTALLATION

- wall or ceiling mounted with universal mounting bracket (included with unit)

### WARRANTY

- three years

#### IDEAL FOR:

construction site, garage, workshop, small commercial space

°**STELPRO**

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website [www.stelpro.com](http://www.stelpro.com).



## TECHNICAL SPECIFICATIONS

WITHOUT CONTROL	BUILT-IN THERMOSTAT	24 V CONTROL	POWER	VOLTAGE	FLOW	THROW DISTANCE		HEAT RISE		WEIGHT	
CODE	CODE	CODE	WATT S	VOLTS	CFM	M	FT	°C	°F	KG	LB
RUH2CHAR	RUH2TCHAR	RUH2C24CHAR	2000/1500	240/208	350	3	10	10	18	9	20
RUH3CHAR	RUH3TCHAR	RUH3C24CHAR	3000/2250	240/208	350	3	10	15	27	9	20
RUH4CHAR	RUH4TCHAR	RUH4C24CHAR	4000/3000	240/208	350	3	10	20	36	9	20
RUH5CHAR	RUH5TCHAR	RUH5C24CHAR	5000/3750	240/208	350	3	10	25	45	9	20

## TECHNICAL DRAWINGS

