

Plug socket with cable KMEB-2-24-2,5-LED

Part number: 174844

FESTO



Data sheet

| Feature | Value |
|--|--|
| Switching position indicator | LED |
| Type of mounting | On solenoid valve via M2.5 central screw |
| Mounting position | optional |
| Product weight | 200 g |
| Electrical connection | 4-pin Angled socket Type C To DIN EN 175301-803 |
| Nominal operating voltage DC | 24 V |
| Protective conductor connection | Available |
| Cable length | 2.5 m |
| Cable diameter | 6.2 mm |
| Cable structure | 3 x 0.75 mm ² |
| Degree of protection | IP65 To IEC 60529 |
| Ambient temperature | -20 °C...80 °C |
| CE mark (see declaration of conformity) | In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Material cable sheath | TPE-U(PUR) |
| Material housing | PA POM |
| Material electrical contact | Bronze |