

# Push-in T-fitting

## QST-1/8-10

Part number: 190667

**FESTO**



## Data sheet

| Feature                                                   | Value                                                                 |
|-----------------------------------------------------------|-----------------------------------------------------------------------|
| Size                                                      | Standard                                                              |
| Nominal size                                              | 6 mm                                                                  |
| Type of seal on screwed plug                              | Coating                                                               |
| Mounting position                                         | optional                                                              |
| Design                                                    | T-shape<br>Push-pull principle                                        |
| Size of pack                                              | 10                                                                    |
| Operating pressure complete temperature range             | -0.095 MPa...0.6 MPa<br>-0.95 bar...6 bar<br>-13.775 psi...87 psi     |
| Temperature-dependent operating pressure                  | -0.095 MPa...1.4 MPa<br>-0.95 bar...14 bar<br>-13.775 psi...203 psi   |
| Note on operating pressure                                | Water: max. 0.6 MPa at max. 50°C                                      |
| Operating medium                                          | Compressed air to ISO 8573-1:2010 [7:-:-]<br>Water (liquid, ice-free) |
| Note on operating and pilot medium                        | Lubricated operation possible                                         |
| Corrosion resistance class CRC                            | 1 - Low corrosion stress                                              |
| LABS (PWIS) conformity                                    | VDMA24364-B1/B2-L                                                     |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1                                      |
| Ambient temperature                                       | -10 °C...80 °C                                                        |
| Product weight                                            | 25 g                                                                  |
| Number of outputs                                         | 2                                                                     |
| Number of supply lines                                    | 1                                                                     |
| Type of mounting                                          | External hexagon, size 12 mm                                          |
| Pneumatic connection, port 1                              | Male thread R1/8                                                      |
| Pneumatic connection, port 2                              | For tubing outside diameter of 10 mm                                  |
| Colour of release ring                                    | Blue                                                                  |
| Material screwed plug                                     | Nickel-plated brass                                                   |
| Note on materials                                         | RoHS-compliant                                                        |
| Material housing                                          | PBT                                                                   |
| Material release ring                                     | POM                                                                   |
| Material tubing seal                                      | NBR                                                                   |

| Feature                         | Value                      |
|---------------------------------|----------------------------|
| Material tubing clamp component | High-alloy stainless steel |