

# Push-in T-fitting QBT-3/8-5/16-U

Part number: 533318

FESTO



## Data sheet

| Feature                                       | Value                                                          |
|-----------------------------------------------|----------------------------------------------------------------|
| Size                                          | Standard                                                       |
| Nominal size                                  | 0.236 in                                                       |
| Type of seal on screwed plug                  | Coating                                                        |
| Mounting position                             | optional                                                       |
| Design                                        | T-shape<br>Push-pull principle                                 |
| Size of pack                                  | 5                                                              |
| Operating pressure complete temperature range | 0.095 MPa...1 MPa<br>0.95 bar...10 bar<br>13.775 psi...145 psi |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-]                      |
| Note on operating and pilot medium            | Lubricated operation possible                                  |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                                       |
| LABS (PWIS) conformity                        | VDMA24364 zone III                                             |
| Ambient temperature                           | 0 °C...60 °C<br>32 °F...140 °F                                 |
| Product weight                                | 1.07 oz                                                        |
| Type of mounting                              | External hex 11/16                                             |
| Pneumatic connection, port 1                  | Male thread 3/8 NPT                                            |
| Pneumatic connection, port 2                  | For tubing outside diameter of 5/16"                           |
| Colour of release ring                        | grey                                                           |
| Note on materials                             | RoHS-compliant                                                 |
| Material housing                              | Brass, nickel-plated<br>PBT                                    |
| Material thread seal                          | PTFE                                                           |
| Material release ring                         | POM                                                            |
| Material tubing seal                          | NBR                                                            |
| Material tubing clamp component               | High-alloy stainless steel                                     |