

Electrical sub-base VAVE-L1-1VR8-LP

Part number: 573919

FESTO



Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V 24 V
Immunity to surge	0.8 kV
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-5 °C...60 °C
Mounting position	optional
Max. tightening torque	0.27 Nm
Product weight	3.2 g
Electrical connection	3-pin/2-pin M8/- Plug connector/socket
Protective conductor connection	Not available
Type of mounting	On solenoid valve via self-tapping screw
Housing colour	Black
Note on materials	RoHS-compliant
Material cover	PA
Material seals	EPDM
Material housing	PA
Material screws	Tempered steel