



## MODbox™ Rechargeable Worklight



The MODbox™ Area Light is a work light designed for any jobsite, with up to 1000 Lumens of output. The portable light has a MODbox™ compatible kickstand which includes 4 powerful magnets and a nail notch to mount light for hands-free use. These versatile mounting features along with a 360-Degree rotating light head allow users to direct the light where needed. The area light has 3 light output modes, with a run time of up to 21 hours and is impact-resistant, capable of surviving a 9-Foot drop.

### Specifications

Type:	Work Light	Application:	Medium Spread Light Coverage
Special Features:	Pivoting Hinge, Rotating Head, Magnets, Nail Hole	Overall Length:	3.59" (9.1 cm)
Overall Height:	4.59" (11.7 cm)	Overall Width:	2.71 (6.9 cm)
Material:	Plastic	Color:	Orange/Black
Bulb Type:	LED	Lumens:	Per Mode; 1000, 425, or 300
Battery Life:	Per Mode: 9, 14, or 21 hr	Batteries:	Lithium-Ion
Temperature Range:	-4? to 122? F (-20? to 50? C)	Drop Protection:	9.8' (3 m)
Water Resistant:	Yes	Strobing:	No
Shock Resistant:	No	Included:	Charging Cable
Weight:	1.21 lb (0.55 kg)		