



# MODbox™ Rechargeable Dual Beam LED Work Light



The MODbox™ Dual Beam Rechargeable Work Light is a 2-in-1 flood and spot light that can operate independently or simultaneously with 360-Degree rotation and up to 3000 lumens of output. This portable light features multiple mounting options for hands-free use including MODbox™ rail compatibility, magnetic base, and hanging hook. This durable LED work light is designed to work on any job site; it is water resistant and suitable for indoor and outdoor use.

## Specifications

Type:	Work Light	Application:	High Spread Light Coverage
Special Features:	Rotating Axel, Magnets, Hook	Overall Length:	8.81" (22.4 cm)
Overall Height:	4.13" (10.5 cm)	Overall Width:	9.13" (23.2 cm)
Material:	Plastic	Color:	Orange/Black
Bulb Type:	LED	Lumens:	Per Mode; 3000, 1400, 700, 475, 250
Battery Life:	12 Hr	Batteries:	Lithium-Ion
Temperature Range:	41°F to 95°F (5°C to 35°C)	Drop Protection:	3m (9.8')
Water Resistant:	Yes (IP65)	Strobing:	No
Shock Resistant:	No	Spotlight:	LED
Included:	Battery, USB-C Charging Cable	Weight:	2.2 lb (1 kg)