



Ceramalux ALTO

SON 250W E39 ED58 CL SLV/12

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Luminous Efficacy (rated) (Nom)	114 lm/W
Chromaticity Coordinate X (Nom)	523
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Color rendering index (CRI)	26
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3.0 A
Voltage (Nom)	95 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Approval and Application	
Mercury (Hg) Content (Max)	23.5 mg
Product Data	
Order product name	SON 250W E39 ED58 CL SLV/12
Full product name	SON 250W E39 ED58 CL SLV/12
Order code	928601139401
Material Nr. (12NC)	928601139401
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.187 kg
EAN/UPC - Product/Case	046677368791
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677368796

Ceramalux ALTO

Dimensional drawing

Product	D	C (max)
SON 250W E39 ED58 CL SLV/12	57.2 mm	248 mm

