

ET120

ELECTRONIC THERMOSTAT – LOW VOLTAGE / 0-10 V



This modulating thermostat with a 0-10 V analog output provides better temperature control for simple commercial HVAC applications.

- **COMPATIBLE WITH THE CIR-048 DUCT HEATER CONTROL CARD (SDHX AND SDHR SERIES)**
- **EASY ACCESS TO TEMPERATURE CONTROL**

COLOUR

- off-white

VOLTAGE

- 24 Vac

CONTROL

- output: 0-10 V

TEMPERATURE RANGE

- between 10 and 32 °C (50 and 90 °F)
- display in Celcius only

WARRANTY

- one year

DESIGNED FOR:



SDHR



SDHX

TECHNICAL SPECIFICATIONS

PRODUCT	DESCRIPTION
ET120	0-10 V electronic thermostat (Celcius only)

DIMENSIONS: 3.27 in. x 3.27 in. x 1.19 in. (83.1 mm x 83.1 mm x 30.2 mm)

°STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.