

UT202NP SERIES NON-PROGRAMMABLE ELECTRONIC THERMOSTAT

ACCESSIBLE AND FRIENDLY

Uniting fast installation with user-friendly installation, the new Uniwatt non-programmable electronic thermostat is the ideal choice for small rooms in your home. The UT202NP can control convectors or baseboards with a power up to 2000 W. In addition, the thermostat has only two buttons, offering you simple and easy temperature setting.



ULTRA PRECISE (± 0.5 °C)

EASY INSTALLATION

FOR BASEBOARDS AND CONVECTORS

COLOUR

white

FINISH

molded plastic

WATTAGE & VOLTAGE

150 W to 1000 W @ 120 V / 260 W to 1730 W @ 208 V / 300 W to 2000 W @ 240 V

CONTROL

- 2-wire connection
- frost-free warning
- lock option at a maximum temperature set point (Security mode)
- display in either Celsius or Fahrenheit

ACCURACY

accurate ambient temperature control of ± 0.5 °C (1 °F)

TEMPERATURE RANGE

between 5 and 30 °C (41 to 86 °F)

WARRANTY

two years

MORE THAN
10%

CONSUMPTION SAVINGS

ENERGY SAVINGS OF MORE THAN 10% COMPARED TO A MECHANICAL THERMOSTAT

DESIGNED FOR



TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY
	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ
UT202NP	150/260/300	1000/1730/2000	120/208/240	8,3	60

DIMENSIONS: width of 3 3/8 in. (85 mm), height of 4 7/8 in. (123 mm) and depth of 1 1/4 in. (31 mm)