

# STF362WF – CONCERTO WI-FI

## FLOOR HEATING THERMOSTAT

CONNECTED – WI-FI



## CONTROL YOUR FLOOR AND YOUR COMFORT FROM ANYWHERE, AT ANY TIME

Our CONCERTO WiFi thermostat is ideal for easily managing your floor heating. Thanks to its intuitive app, you can program and control the temperature from your smartphone, wherever you are. Create personalized schedules to heat your home according to your needs and save energy. Its elegant design blends in perfectly with any décor. Give yourself comfort and peace of mind with the CONCERTO WiFi thermostat, for optimum comfort at all times.

### ■ WIFI CONNECTED THERMOSTAT

CONTROL FROM ANYWHERE, AT ANY TIME

### ■ INSTALLER CONFIGURATION

SIMPLE CONFIGURATION VIA APP USING  
BLUETOOTH®

### ■ SIMPLE CONTROL ON THE THERMOSTAT

ADJUST SETPOINT, CHANGE MODE OR  
SWITCH ON/OFF

### ■ GROUND FAULT CIRCUIT INTERRUPTER (GFCI CLASS A)

PROTECTS USERS AND THE INSTALLATION

### COLOUR

- White

### FINISH

- Moulded plastic

### MANUFACTURING

- Fitted with an integrated ground fault circuit interrupter (GFCI) and a test indicator light.
- Terminal block connection / DPST with 2-pole disconnects
- Floor sensor (15 ft/4.5 m) included\*

### POWER AND VOLTAGE

- Maximum of 1800 W @ 120 V
- Maximum of 3120 W @ 208 V
- Maximum of 3600 W @ 240 V

### CONTROL

- Pre-programmed with four weekday events and two weekend events
- Option to control Floor temperature (F), Room temperature (R) or Room with Floor limit (RF)
- Possibility of setting a maximum temperature setpoint (to protect the floor and users)
- Temperature can be displayed in degrees Celsius or Fahrenheit

### PRECISION

- Precise control of floor or ambient air temperature
- Temperature reading with thermistor

### TEMPERATURE RANGE

- Floor: 5 to 40°C (41 to 104°F)
- Ambient: 0 to 40°C (32 to 104°F)

### WARRANTY

- Three years

\*This thermostat is also compatible with floor sensors produced by other manufacturers.

### COMPATIBLE WITH

Compatible with  
Amazon Alexa

works with  
Google Home

## TECHNICAL SPECIFICATIONS

PRODUCT	WATTS	VOLTAGE	AMPERAGE	FREQUENCY	GFCI
CODE	MAXIMUM	VOLTS	AMPS	HZ	MA
STF362WF	1800/3120/3600	120/208/240	15	50/60	5

# °STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website [www.stelpro.com](http://www.stelpro.com).