

Adapter
AD-1/8NPT-G1/8-I
Part number: 9624

FESTO



Data sheet

Feature	Value
Nominal size	5.95 mm
Operating pressure complete temperature range	-0.95 bar...10 bar
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque pneumatic connection 1	7 Nm
Max. tightening torque pneumatic connection 2	6 Nm
Product weight	9.5 g
Pneumatic connection, port 1	Male thread 1/8 NPT
Pneumatic connection, port 2	Female thread G1/8
Note on materials	RoHS-compliant
Material seals	PVC
Material housing	Galvanised steel