

Benefits

Mongoose Clamps are designed for use with common cable, conduit, pipe, and tube sizes. These clamps are commonly used for cable, trapeze, and wall supports.

- Ready to install out of the box with no assembly time on the jobsite
- Hex-head universal bolt for fast, single-handed installation with nut-driver or screwdriver
- Universal Clamp for maximum flexibility and industry approval for cables, EMT, Rigid Conduit, and more
- Strut hooks assure parallel alignment of cables and conduits

Features

- One-piece saddle design
- UL Listed
- Cable and Pipe Clamp
- Easy Installation for labor savings; no assembly
- Adjustable
- Electro-galvanized plating
- 14 gauge (½" through 2");
12 gauge (2 ½" through 4")



Mongoose Universal One-Piece Cable, Pipe, Conduit (GRC, EMT, & IMC) and Tubing Clamps

Part Number	Nominal Trade Size EMT/Rigid		Cable O. D.				Bolt Size	Qty per Box	Static Load Limit (lb) - Safety Factor = 4
	in	mm	Min		Max				
			in	mm	in	mm			
MPC050 EG	½	12.7	0.500	12.7	0.890	22.6	5/16"-18 UNC x 1"	100	200
MPC075 EG	¾	19.1	0.860	21.8	1.110	28.2	5/16"-18 UNC x 1"	100	200
MPC100 EG	1	25.4	1.110	28.2	1.400	35.6	5/16"-18 UNC x 1"	100	200
MPC125 EG	1 ¼	31.8	1.400	35.6	1.725	43.8	5/16"-18 UNC x 1"	50	200
MPC150 EG	1 ½	38.1	1.690	42.9	1.980	50.3	5/16"-18 UNC x 1"	50	200
MPC200 EG	2	50.8	1.980	50.3	2.576	65.4	5/16"-18 UNC x 1-1/2"	50	200
MPC250 EG	2 ½	63.5	2.576	65.4	3.060	77.7	5/16"-18 UNC x 1-1/2"	25	350
MPC300 EG	3	76.2	3.060	77.7	3.626	92.1	5/16"-18 UNC x 1-1/2"	25	350
MPC350 EG	3 ½	88.9	3.626	92.1	4.126	104.8	5/16"-18 UNC x 1-1/2"	25	350
MPC400 EG	4	101.6	4.126	104.8	4.626	117.5	5/16"-18 UNC x 1-1/2"	25	350