



Catalog Number
Notes
Type

Contractor Select™

OLB

LED Bullet Floodlight

The OLB LED bullet floodlight comes ready to handle all accent lighting applications. Eliminate jobsite complexity with this single SKU solution that delivers dependable, adaptable illumination.

FEATURES:

- Dual Layered Lens:
 - 5X5 (50°)
 - 3X3 (20°)
- Switchable CCT
- Adjustable Lumen Output
- Selectable On/Off Dusk to Dawn Photocell
- Multiple Mountings Included



5X5 (50° Flood Optic



3X3 (20° Spot



Catalog Number	CI CODE	UPC	Lumens	Wattage	Voltage	CCT	Finish	Replaces Up To	Pallet Quantity
OLB ALO SWW2 UVOLT PE DDB	*2938JY	198935110601	500/750/1000LM	8.4	120-347V	3000K/4000K/5000K	DDB	75W	288

Nominal Lumens	3000K		4000K		5000K	
	Output	Wattage	Output	Wattage	Output	Wattage
High	989LM	8.7W	1,069LM	8.4W	1,074LM	8.8W
Medium	755LM	6.5W	802LM	6.2W	810LM	6.5W
Low	488LM	4.2W	514LM	4.1W	530LM	4.3W



Specifications

INTENDED USE:

The OLB floodlight is designed to provide a cost effective, energy-efficient solution for a variety of applications with up to 1000 lumens. OLB is well suited for general illumination of signage, flagpoles, yards, walkways, landscaping, and other floodlighting applications.

CONSTRUCTION:

Die cast aluminum housing with dark bronze powder paint finish for lasting durability.

OPTICS:

Optics are engineered for superior field-to-beam ratios, uniformity and spacing. Equipped with both 5X5 (50°) flood optics for illuminating larger objects and 3X3 (20°) spot optics for illuminating targets up to 50 feet away.

ELECTRICAL:

OLB features adjustable low, medium and high lumen output. Switchable CCT selections include 3000K (warm), 4000K (cool) or 5000K (daylight) at 80CRI and a selectable dusk to dawn photocell that automatically turns the fixture on in the evening and off the next morning. OLB luminaires operate at 120-347V (UVOLT). System Power Factor >90%, THD <20%. L90>50,000 hrs at 25°C ambient.

INSTALLATION:

The OLB ships standard with a 1/2" NPS threaded knuckle. Each floodlight includes a round electrical cover mounting plate and ground stake.

LISTINGS:

CSA certified to US and Canadian safety standards. IP66 Rated and suitable for use in -40°C minimum ambient. DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List a www.designlights.org/QPL to confirm which versions are qualified.

WARRANTY:

5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.

Luminaire	Depth (D)	Width (W)	Height (H)	Fixture Weight
OLB	4" (109cm)	3" (67cm)	8" (191.45cm)	5lbs (2.27kg)

