



PRODUCT-DETAILS

OHB65L10B

OHB65L10B HANDLE

General Information

Extended Product Type:	OHB65L10B
Product ID:	1SCA141836R1001
EAN:	6417019713014
Catalog Description:	OHB65L10B HANDLE
Long Description:	OHB65L10B HANDLE
Display Name:	OHB65L10B

Material Compliance

Conflict Minerals Reporting Template (CMRT):	9AKK108467A5658
REACH Declaration:	1SCC011021D0201
RoHS Declaration:	1SCC011020D0201
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Popular Downloads

Data Sheet, Technical Information:	No documentation needed
Instructions and Manuals:	1SCC390022M0020

Environmental

Degree of Protection:	IP66
-----------------------	------

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85389099

Country or Territory of Origin:	Estonia
---------------------------------	---------

Dimensions

Product Net Width:	98 mm
Product Net Height:	45 mm
Product Net Depth / Length:	66 mm
Product Net Weight:	0.135 kg

Container Information

Package Level 1 Units:	bag 1 piece
Package Level 1 Width:	65 mm
Package Level 1 Depth / Length:	80 mm
Package Level 1 Height:	66 mm
Package Level 1 Gross Weight:	0.14 kg
Package Level 1 EAN:	6417019713014

Technical

Color:	Black
Handle Color:	Black
Handle Length:	65 mm
Handle Type:	Pistol

Certificates and Declarations

Declaration of Conformity - CE:	1SCC390030D2704
---------------------------------	-----------------

External Classifications and Standards

UNSPSC:	39122221
IDEA Granular Category Code (IGCC):	5219 >> Switch part or accessory
WEEE Category:	Product Not in WEEE Scope

Categories

Products > Low Voltage Products and Systems > Switches > Switch Disconnectors