



Project / Job Name:

Location:

Fixture Type:

Notes:

65-933 - Starfish; Smart Doorbell Security Camera
Wired; White Doorbell With White Chime; White Finish



GENERAL

Company	NUVO
EA Height	6.14
EA Width	3.94
EA Length	2.17
Mounting Height	5.5
Mounting Width	1.5
Camera Resolution	3MP(1536x2048)
Starfish Communication Protocol	WiFi-2.4GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Extends (in)	1.18
Material	Plastic (PS)
Fixture Type	Security Camera
Camera Focal Length	2.5
Camera Image Compression	H.264/H.265
Includes	Mounting Bracket; Screws and Anchors; USB-C Cable
Product Notes	USB-C Cord Length: 19.69 Inches; Wire Lead Cord Length: 19.69 Inches
Status	Active
Camera Storage Capacity	128GB
Style	Utility
Camera Viewing Angle	170 Degrees
Starfish Voice Assistants Supported	Alexa, Google Home, Siri
CCT Selectable	False
Wattage Selectable	False
Finish Family	White
Amps	1.000A
Camera Audio	2-Way Communication
Has Camera	True
IOT Enabled	True
Starfish Operational Humidity	10% to 95% non-condensing
Photo Cell	Has Photocell
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Starfish Software Upgradeable	True
Indoor Outdoor	Outdoor
Product Technology	Not Applicable

ELECTRICAL

Dimmable	Non-Dimmable
Operating Temp	-20C (-4F) to +50C (+122F)
Volts	5.1V

PHYSICAL

Finish	WHITE
--------	-------

ADDITIONAL INFO

Warranty	1-Year
----------	--------

FEATURES

Camera Night Vision	IR Distance 5m
---------------------	----------------

PACKAGING

UPC	045923411717
Case Cube	1.1372
Case Height	7.17
Case Length	12.6
Case Quantity	12
Case UPC	10045923411714
Case Weight	11.24
Case Width	9.37
EA Cube	0.0304
EA Height	6.14
EA Length	2.17
EA Quantity	1
EA Weight	0.77
EA Width	3.94
Pack Type	Color Box
Web Height	5.87
Web Width	1.85

COMPLIANCE

ADA Compliant	False
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
Dark Sky Rated	False
FCC Compliant	True
IP Rating	IP65
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
CA Compliance Text	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24 Compliant	False