



Project / Job Name:

Location:

Fixture Type:

Notes:

S11570 - 13 Watt; LED Retrofit Downlight; 5-6 Inch Round; Starfish IOT; RGB & Tunable White; 120 Volt; 90 CRI; White Finish



GENERAL

Company	SATCO
EA Height	7.36
EA Width	3.54
EA Length	7.48
Bulb Included	Integrated
Starfish Communication Protocol	WiFi-2.4GHz
Diameter	7.32
Dimmable Text	Only with Starfish App
Material	Aluminum
Fixture Type	Downlight Retrofit
Includes	E26 Adapter included (S9001)
Status	Active
Style	Utility
Total Harmonic Distortion	<30%
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
CCT Selectable	True
Wattage Selectable	False
Can Size	5-6 in.
Finish Family	White
Amps	0.108A
Has Camera	False
IOT Enabled	True
Lens Finish	Frosted
Lens Material	Polycarbonate (PC)
Power Factor	>0.9
SDS Class	LED_Fixture
Starfish Software Supported	Tuya/Starfish App
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	65W

ELECTRICAL

CCT (Kelvin Temp)	2000K-5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	110
Color Temp	Warm to Cool White/Color Changeable
CRI	90+
Dimming Type	Smart-Starfish App only
Operating Frequency	60Hz
Operating Temp	-20C (-4F) to +40C (+104F)
Lumens	850L
Volts	120v
Watts	13W

PHYSICAL

Lamp Base	Medium Adapter
Finish	WHITE
ANSI Base	E26 Adapter
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923115707
Case Cube	1.5861
Case Height	15.51
Case Length	15.75
Case Quantity	12
Case UPC	10045923115704
Case Weight	9.96
Case Width	11.22
EA Cube	0.1128
EA Height	7.36
EA Length	7.48
EA Quantity	1
EA Weight	0.64
EA Width	3.54
Inner Cube	0.0
Inner Height	0.0
Inner Length	0.0
Inner Quantity	0
Inner Weight	0.0
Inner Width	0.0
Pack Type	Box
Web Height	3.03
Web Width	7.32

COMPLIANCE

Air Tight	True
CA Regulations	T20 Non-Compliant - LPW <80
CA Prop 65	Lead
CA Status	Non-Compliant
FCC Compliant	True
IC Rated	True
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
CA Compliance Text	Non-Compliant
DLC Approved	False
Energy Star Certified	No
Title 20	No
T24 Compliant	False