



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

65-900R1 - Starfish; Bullet SMART Security Light w/Camera; 20 Watt; 3000K CCT; White Finish; 120-277 Volt



GENERAL

Company	NUVO
EA Height	9.92
EA Width	9.65
EA Length	9.45
Bulb Included	Integrated
Camera Resolution	3MP(2304x1296)
Starfish Communication Protocol	WiFi-2.4GHz; WiFi-5GHz; 802.11b/g/n; WPA/WPA2; WPA-PSK/WPA2-PSK
Dimmable Text	Only with Starfish App
Extends (in)	9.45
Material	Die-cast Aluminum
Fixture Type	Security Camera
Camera Focal Length	2.9
Camera Image Compression	H.264/H.265
Camera Image Sensor	1/2.7 Color CMOS
Status	Active
Camera Storage Capacity	32GB SD Card Included; Optional 128GB Max SD Card
Style	Utility
Surge Protection	Built-in surge protection - 2KV
Camera Viewing Angle	135 D; 109 H; 58 V
Starfish Voice Assistants Supported	Alexa, Google Home, Siri, SmartThings
CCT Selectable	False
Wattage Selectable	False
Finish Family	White
Additional Info	For Non IOT Version See 65-710, 65-711, 65-716, 65-717
Amps	0.167-0.072A
Camera Audio	2-Way Communication
Has Camera	True
IOT Enabled	True
Lens Finish	Frost
Lens Material	Glass
Starfish Operational Humidity	20% to 85% non-condensing
Photo Cell	Has PIR Sensor
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Starfish Software Supported	AWS Cloud Security Servers, Tuya/Starfish App
Indoor Outdoor	Outdoor
Product Technology	LED
Incandescent Equivalent	100W

PACKAGING

UPC	045923404382
Case Cube	2.264
Case Height	10.32
Case Length	41.34
Case Quantity	5
Case UPC	10045923404389
Case Weight	17.64
Case Width	9.17
EA Cube	0.5235
EA Height	9.92
EA Length	9.45
EA Quantity	1
EA Weight	3.09
EA Width	9.65
Pack Type	Color Box
Web Height	8.46
Web Width	8.27

COMPLIANCE

ADA Compliant	False
CA Regulations	T20 Exempt - Fixtures Not Regulated
CA Prop 65	Lead
CA Status	Lawful for sale in California
FCC Compliant	True
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
CA Compliance Text	Lawful for sale
Title 20	Exempt
T24 Compliant	False

ELECTRICAL

CCT (Kelvin Temp)	3000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	50
Color Temp	Soft White
CRI	80+
Dimming Type	Smart-Starfish App only
Operating Frequency	60Hz
Operating Temp	-30C (-22F) to +50C (+122F)
Lumens	1900L
Volts	120V-277V
Watts	20W

PHYSICAL

Lamp Base	Integrated
Finish	WHITE
ANSI Base	Integrated
Lamp Type	Integrated LED

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	May be wired to recessed or external junction boxes.

FEATURES

Camera Night Vision	10 pcs; 850nm; LED; IR Distance 10m
---------------------	-------------------------------------